



## Boring bar blank Form A, BT 40, Dimension A: 250 mm



### Order data

Order number	302889 250
GTIN	4062406105044
Item class	32A

### Description

#### Version:

Taper with collar, hardened and ground. Soft shank for further machining.

#### Optional extras:

Pull studs (PS) No. 308760 – 308806.

Shape: A

External Ø D: 63 mm

### Technical description

External Ø D	63 mm
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A
Type of product	Boring bar blank

### Accessories

Pull stud Hurco 90° with bore and fit sealed suitable for steep tapers 40

308805 40

Pull stud Hurco 60° with fit sealed suitable for steep tapers 40	308804 40
Pull stud Hurco 45° with fit sealed suitable for steep tapers 40	308802 40
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Wrench for pull studs ISO 7388 suitable for steep tapers 40 SK	308830 40
Pull stud 60° sealed suitable for steep tapers 40	308785 40
Pull stud 90° sealed suitable for steep tapers 40	308795 40
Hurco 60° pull stud with bore and fit sealed suitable for steep tapers 40	308803 40
Wrench for pull studs DIN ISO 7388-1 (formerly DIN 69872) suitable for steep tapers 40 SK	308820 40
Pull stud Hurco 90° with fit sealed suitable for steep tapers 40	308806 40
Pull stud Hurco 45° with bore and fit sealed suitable for steep tapers 40	308801 40
Torque insert for Pull studs to DIN 69872 suitable for steep tapers 40 SK	308810 40
Pull stud 45° sealed suitable for steep tapers 40	308765 40
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Torque insert for Pull studs to SO 7388 suitable for steep tapers 40 SK	308812 40
Pull-stud 60° sealed suitable for steep tapers 40	308780 40