



Digital caliper ABS + accessories set, Measuring range: 150mm



Order data

Order number	412815 150
GTIN	4062406156497
Item class	42A

Description

Version:

Set consisting of a digital caliper and accessories set.

- **Digital caliper with absolute scale, no zeroing required. Large high-contrast digital display. The measuring faces are precision-lapped. With sturdy metal casing.**
- **Accessories set for digital caliper – permits measurement of recesses, slots and pitches between holes.**

Supplied with:

1× accessory set No. 412747 size 3.5 **consisting of:**

2 pairs of contact point carriers short and long.

3 pairs of measuring tips with measuring discs Ø 6 mm, Ø 10 mm, Ø 12.5 mm.

2 pairs of measuring tips with anvil cones Ø 9 mm, 60° and Ø 12 mm, 60°.

1 pair of measuring tips with measuring cylinders Ø 1.5×9 mm.

1× spring system for constant gauging force.

1× hexagon key L-wrench.

1× depth extension base 75 mm.

Supplied in a sturdy plastic box.

1 battery No. 081560 size CR2032.

1× digital caliper No. 412821 size 150.

Technical description

#Number of batteries contained	1
Measured value saving	once-off setting of the zero position
Scale divisions	0.0005 in

Data sheet

Jaw length	40 mm
Calibration	A1
Standard	ISO 13385
Scale divisions	0.01 mm
Measuring range	0 - 150 mm
#Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement face	precision lapped
Depth gauge available	yes
Reversible reading	mm / inch
Depth gauge	rectangular 3.7×1.3
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/412815-150>