



PNEG 1106XNER-W Wiper, CA420M, Type: GG



Order data

Order number	223324 GG
GTIN	4960664732975
Item class	25A

Description

Version:

10-edge pentagonal indexable inserts for stable and economical machining.

W - 2-edge wiper insert.

Note:

Standard application values for $a_e = 0.3 \times D$.

Plane edge: 10 mm

Feed f_z per tooth: max. 0.2 mm

Technical description

Feed f_z per tooth	max. 0.2 mm
maximum cutting depth $a_{p,max}$ when side milling	6 mm
maximum cutting depth $a_{p,max}$ when slot milling from solid	6 mm
Series	Face mill
ISO code indexable insert	PNEG 1106XNER-W
Grade	CA420M

Tool material	Carbide
Plane edge	10 mm