

HOLEX®
External micrometer, Measuring range: 0-25 mm

Order data

Order number	423010 0-25
GTIN	4045197204066
Item class	42B

Description
Version:

With conical anvil for measuring the wall thickness of pipes and other curved parts. Measuring spindle with carbide-tipped anvils, anvil \varnothing 8 mm, hardened. With hand temperature insulated frame, locking lever, and high quality ratchet.

Packaging: sturdy box

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Scale divisions: 0.01 mm

Spindle \varnothing : 6.5 mm

Spindle pitch: 0.5 mm

Technical description

Micrometer barrel graduations	1/50 mm
Spindle \varnothing	6.5 mm
Measuring range	0 - 25 mm
Spindle pitch	0.5 mm
Scale divisions	0.01 mm
Calibration	B1
Norm	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	Special external micrometer

Services

Calibration External tube micrometer maximum measuring range 25 mm	012050 25
Labelling laser-etched Type	018940
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100