

**HOLEX®**
**Micrometer with dial comparator, Measuring range: 0-25 mm**

**Order data**

Order number	422510 0-25
GTIN	4045197203991
Item class	42B

**Description**
**Version:**

Measuring spindle through hardened and ground.

With precision lapped **carbide tipped anvils**.

Spindle and anvil of stainless steel.

One piece frame and spindle guide.

Button for retracting the measurement anvil for repetitive measurements.

With adjustment screw for zeroing.

Tolerance pointers for good/ reject measurements.

With hand temperature protection. Lever for spindle clamping.

**Callout:**

Deviation read-off in 1/1000 mm.

Push button for anvil retraction.

**Accuracy:**

**Dial comparator 1 µm – micrometer 3 µm.**

**Supplied with:**

Adjustment wrench.

Calibration: B9

Measuring range dial comparator: ±0.045 mm

Graduation of the micrometer: 0.01 mm

Graduation of the precision dial comparator: 0.001 mm

Clearance depth of micrometer frame: 18 mm

**Technical description**

Measuring range dial comparator	±0.045 mm
---------------------------------	-----------

Graduation of the micrometer	0.01 mm
Graduation of the precision dial comparator	0.001 mm
Measuring range	0 - 25 mm
Clearance depth of micrometer frame	18 mm
Norm	DIN 863
Micrometer barrel graduations	1/50 mm
Measurement technology	analogue
Packaging	sturdy box
Calibration	B9
Type of product	Micrometer with dial comparator

## Services

Calibration Indicator micrometer maximum measuring range 25 mm	012240 25
Labelling laser-etched Type	018940