

## Standing stool, height adjustable, Gas pressure spring



### Order data

|              |               |
|--------------|---------------|
| Order number | 965631        |
| GTIN         | 2050000981364 |
| Item class   | 96B           |

### Description

#### Version:

Tubular steel frame with anti-slip, oil-resistant glides. Seat height adjustable by locking lever.

**Seat of PU foam.** Adjustable seat angle and pivotable to either side with automatic return adjustment.

Height adjustment of the seat by **gas pressure safety spring**.

#### Standard:

**DIN 68877**

#### Colour:

Black RAL 9005.

Load capacity chair: 120 kg

Height adjustment range: 645 - 825 mm

Seat width: 320 mm

Seat depth: 220 mm

Colour of seat material: black

### Technical description

|                         |        |
|-------------------------|--------|
| Colour of seat material | black  |
| Seat width              | 320 mm |

|                           |                         |
|---------------------------|-------------------------|
| Height adjustment version | Gas pressure spring     |
| Standard                  | DIN 68877               |
| Support frame version     | Base frame              |
| Seat depth                | 220 mm                  |
| Material of base          | Steel                   |
| Material of seat surface  | PU foam                 |
| Seat tilt adjustment      | yes                     |
| Type of height adjustment | Height adjustment lever |
| Load capacity chair       | 120 kg                  |
| Footprint width           | 650 mm                  |
| Footprint depth           | 450 mm                  |
| Height adjustment range   | 645 - 825 mm            |
| Type of product           | Standing stool          |

---

## Accessories

|                                |          |
|--------------------------------|----------|
| Seat for standing stool Type S | 963901 S |
|--------------------------------|----------|