



Shockwave Helix Drill Bit Set - 10 pieces

Titanium coating for up to 3x life vs. black oxide
Shockwave impact duty, engineered for drills and impacts
Red helix design for rapid chip removal
Chip breaker decreased heat buildup
135 split point for precision start no walking
Best in class drilling

Includes

- (2) 1/8" Titanium SHOCKWAVE™ (48-89-4605)
- (1) 9/64" Titanium SHOCKWAVE™ (48-89-4606)
- (1) 5/32" Titanium SHOCKWAVE™ (48-89-4607)
- (1) 11/64" Titanium SHOCKWAVE™ (48-89-4608)
- (1) 3/16" Titanium SHOCKWAVE™ (48-89-4609)
- (1) 7/32" Titanium SHOCKWAVE™ (48-89-4611)
- (1) 1/4" Titanium SHOCKWAVE™ (48-89-4613)
- (1) 5/16" Titanium SHOCKWAVE™ (48-89-4617)
- (1) 3/8" Titanium SHOCKWAVE™ (48-89-4621)



U07080 48894633

U07080 48894633

Shockwave Drill Bit Set - 10 pieces

21.72



Nut Driver Set - 7 pieces

Universal driver head fits 4X more fasteners. Removes rusted and stripped bolts. 3" Hollow Shaft Depth - Ideal for long bolts or threaded rod applications. Wrench Ready HEX shanks deliver additional leverage.

Chrome Plated - Marine Grade Rust Protection. Forged steel shanks provide longer life and more durability. Deep well sockets - Drive multiple fasteners. Multiple ID Markings allow for quick tool identification on jobsite.

Includes:

- (1) 1/4" Hollow Shaft Nut Driver (48-22-2421)
- (1) 5/16" Hollow Shaft Nut Driver (48-22-2422)
- (1) 11/32" Hollow Shaft Nut Driver (48-22-2423)
- (1) 3/8" Hollow Shaft Nut Driver (48-22-2424)
- (1) 7/16" Hollow Shaft Nut Driver (48-22-2425)
- (1) 1/2" Hollow Shaft Nut Driver (48-22-2426)
- (1) 9/16" Hollow Shaft Nut Driver (48-22-2427)



U62003 2407

U62003 2407

Nut Driver Set - 7 pieces

37.26



SERVICE COMPETENCE

- Highly qualified technical knowledge
- Machining specialists
- Workstations and storage specialists
- First-class advice for you on site