

Magnetic Torpedo Laser Level

Model #: 40-6184
UPC: 049448061846



This magnetic torpedo laser level offers precision, versatility and durability with four vials that read plumb, level, 45° and cross check as well as three simultaneous 90° laser beams for level, plumb and square reference points. For versatility, the level comes equipped with a strong magnetic leveling base, tripod mount and V-groove frame that fits on pipe and conduit. And the precision crafted, anodized aluminum frame provides maximum accuracy and durability. The level also comes with a soft-sided carrying pouch to keep your tool clean and safe when not in use.

PRODUCT DETAILS

40-6184 Includes > Laser, base (leveling bracket), 3 "AA" alkaline batteries, two mounting straps, and soft-sided pouch

- Precision crafted anodized, machined aluminum frame for superior accuracy and durability
- Four vials read plumb, level, 45°, and cross check
- Strong magnetic base, tripod mount, and v-groove frame for maximum versatility
- Leveling base included

SPECIFICATIONS

Accuracy	±1/8"/50'
Battery Life	50 hours
Center Screw Thread	1/4"-20
Dimensions	3.12" x 9.87" x 1.60"
Laser Classification	Class IIIa
Laser Wavelength	650nm±10nm
Leveling Method	Manual (Vials)
Maximum Power Output	≤5mW
Power Supply	3 AA Alkaline Batteries (included)
Warranty	3 Years
Weight	1.60 lbs
Working Range	Up to 100'
Working Temperature	14°F-113°F



APPLICATION

Torpedo levels are designed for use in tight spaces and for projecting the laser over long distances, making this laser level ideal for jobsite layout, concrete formwork, plumbers, electricians, HVAC and more.



For additional information on Johnson products, please contact
Customer Service at 888.953.8357 or service@johnsonlevel.com
www.johnsonlevel.com | © Johnson Level & Tool Mfg. Co. Inc.