


**Transport equipment**

## Product data sheet

Article no.: 1100 Wheels with pneumatic tyres (max. 400 kg capacity)



Smooth running on rough surfaces, esp. outdoors. Available for trolley width from 600 mm. Additional charge compared to standard wheels.

### Technical Details:



<b>Wheel size (mm)</b>	220 x 70
<b>Tyres</b>	Pneumatic
<b>Note</b>	surcharge on wheels Ø 200 mm
<b>Weight (kg)</b>	0,8
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976011004