


Transport equipment

Product data sheet

Article no.: 1132/7016 Collapsible cart "GREY EDITION"



Tubular steel construction, powder coated anthracite grey, with platform made of derived timber material boards. Surface grey. Handlebar foldable onto platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	720
Width of usable platform (mm)	450
Height of loading platform (mm)	205
Total length (mm)	815
Total width (mm)	470
Total height (mm)	930
Tyres	TPE
Wheel size (mm)	125 x 32
Note	Dimensions folded: 780 x 470 x 283 (LxWxH mm)
Weight (kg)	16
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976311326