


Transport equipment

Product data sheet

Article no.: 1140 Collapsible cart



Tubular steel construction, powder coated, with platform made of derived timber material boards. Surface beech grain. 2 handlebars foldable onto platform. With additional foldable table platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	720
Width of usable platform (mm)	450
Shelf heights (mm)	205, 860
Total length (mm)	900
Total width (mm)	470
Total height (mm)	900
Tyres	TPE
Wheel size (mm)	125 x 32
Note	Dimensions folded: 960 x 470 x 340 (LxWxH mm)
Weight (kg)	26
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011400