


Transport equipment

Product data sheet

Article no.: 1141 Collapsible cart



Tubular steel construction, powder coated, with platform made of derived timber material boards. Surface beech grain. 2 handlebars foldable onto platform. With additional foldable table platform. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	900
Width of usable platform (mm)	600
Shelf heights (mm)	230, 885
Total length (mm)	1080
Total width (mm)	620
Total height (mm)	930
Tyres	TPE
Wheel size (mm)	160 x 40
Note	Dimensions folded: 1320 x 620 x 365 (LxWxH mm)
Weight (kg)	40
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011417