


Transport equipment

Product data sheet

Article no.: 1163 Dolly with gooseneck handle



Made of tubular steel welded and powder coated, blue RAL 5007, with steel sheet platform, flush with frame, handles bolted on. 2 swivel castors and 2 fixed-wheel castors. Wheels with TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	600
Width of usable platform (mm)	500
Height of loading platform (mm)	195
Total length (mm)	890
Total width (mm)	500
Total height (mm)	860
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	14
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976011639