


Transport equipment

Product data sheet

Article no.: 1164/7016 Dolly with gooseneck handle "GREY EDITION"



Made of tubular steel welded and powder coated, anthracite grey RAL 7016, with 2 wooden platforms, handles bolted on. 2 swivel castors and 2 fixed-wheel castors. Wheels with TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 100 kg.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	600
Width of usable platform (mm)	450
Total length (mm)	860
Total width (mm)	450
Total height (mm)	875
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	19
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976611648