


**Transport equipment**

# Product data sheet

Article no.: 1169 Dolly

Frame made of angular steel, welded, powder coated, blue RAL 5007. With wooden platform. 4 swivel castors, wheels with TPE tyres, hubs with precision deep groove ball bearing. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).



## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	600
<b>Width of usable platform (mm)</b>	600
<b>Height of loading platform (mm)</b>	199
<b>Total length (mm)</b>	600
<b>Total width (mm)</b>	600
<b>Total height (mm)</b>	199
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	16
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976011691