Product data sheet

Article no.: 12423 Table top carts



Transport equipment



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. 3 platforms made of antislip waterproof plywood boards (insert type of board). 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle platform 500 kg.

Technical Details:

Warranty (years)

GTIN

Customs tariff number







Total load capacity (kg)	1200
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Shelf heights (mm)	283, 604, 925
Total length (mm)	1410
Total width (mm)	800
Total height (mm)	925
Tyres	Elastic solid rubb
Wheel size (mm)	200 x 50
Weight (kg)	108
Country of origin	Germany