


**Transport equipment**

# Product data sheet

Article no.: 12502 Open cart



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. Platforms and 1 end made of antislip waterproof plywood boards (insert type of board). 2 swivel and 2 fixed-wheel castors, elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	1200
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	700
<b>Height of loading platform (mm)</b>	283
<b>Total length (mm)</b>	1155
<b>Total width (mm)</b>	700
<b>Total height (mm)</b>	283
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 50
<b>Weight (kg)</b>	42
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976125022