


Transport equipment

Product data sheet

Article no.: 1301 Work piece trolley



Sectional steel, with welded wire lattice 75 x 75 mm, powder coated, blue RAL 5007. Continuous platform of derived timber material board, surface beech grain. Wheels: 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel lock. Height of superstructure 1250 mm. Total height 1536 mm. Wire lattice frame inclined at 11%.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Total length (mm)	1372
Total width (mm)	809
Total height (mm)	1536
Angle of inclination (degree)	11
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	90
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976013015