


Transport equipment

Product data sheet

Article no.: 13550 Euro box roller



Compatible for Euro boxes 600 x 400 mm, powder-coated blue RAL 5007. Roller with 2 platforms. Both platforms of derived timber material board housed in frames, rim 10 mm high. Clearance between platforms 390 mm, total height 630 mm. Platforms flush with top edge of frame. 4 swivel castors, TPE tyres, hubs with groove ball bearing. 2 swivel castors with wheel locks, according to European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	605
Width of usable platform (mm)	408
Shelf heights (mm)	209, 638
Load capacity per shelf (kg)	100
Total length (mm)	677
Total width (mm)	414
Total height (mm)	638
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	19
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976213552