Product data sheet

Article no.: 13585 Euro box roller



Transport equipment



Suitable for Euro boxes, 600 x 400 mm, powder coated, blue RAL 5007. Steel plate tray leak-proof welded. Rim 22 mm high. Especially adapted for the transport of open-worked boxes with lubricated or wet parts. Nothing drips on the floor. 4 swivel castors, TPE tyres. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:





Total load capacity (kg)	250
Length of usable platform (mm)	605
Width of usable platform (mm)	408
Height of loading platform (mm)	182
Total length (mm)	615
Total width (mm)	415
Total height (mm)	204
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	13
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976135854