


Transport equipment

Product data sheet

Article no.: 13587 Euro box roller



Compatible for Euro boxes 600 x 400 mm, powder-coated blue RAL 5007. Open angle steel construction with tubular push bar. The face end of the frame opposite the push bar is open (without rim), so that boxes can be drawn on or off. 4 swivel castors, TPE tyres. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Flat packed delivery.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	610
Width of usable platform (mm)	408
Height of loading platform (mm)	182
Total length (mm)	716
Total width (mm)	414
Total height (mm)	970
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	11
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976413587