


Transport equipment

Product data sheet

Article no.: 13600 Drum dolly



For upright transport of 60 litre or 200 litre steel drums. Welded steel construction, powder coated, blue RAL 5007. Interior-Ø 610 mm. 4 swivel castors, 2 with wheel lock. Wheels made of polyamide. Hubs with glide bearing. Handle screw-on type, with 2 eyelets and 1 clamping band.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	420/610
Width of usable platform (mm)	420/610
Total height (mm)	914
Tyres	Polyamide
Wheel size (mm)	80 x 35
Version	offen
Weight (kg)	15,6
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976136004