


Transport equipment

Product data sheet

Article no.: 1361 Drum dolly



For upright transport of 200 litre steel drums. Welded steel construction, powder coated, blue RAL 5007. 4 swivel castors, 2 with wheel lock. Wheels made of polyamide. Hubs with glide bearing. With closed sheet steel save-pan, oil-proof welded. Interior-Ø 630 mm. Rim 80 mm high.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	630
Width of usable platform (mm)	630
Total height (mm)	179
Tyres	Polyamide
Wheel size (mm)	80 x 35
Version	geschlossen
Weight (kg)	15
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976013619