


**Transport equipment**

# Product data sheet

Article no.: 13610 Drum dolly



For upright transport of 200 litre steel drums. Welded steel construction, powder coated, blue RAL 5007. 4 swivel castors, 2 with wheel lock. Wheels made of polyamide. Hubs with glide bearing. With closed sheet steel save-pan, oil-proof welded. Interior-Ø 630 mm. Rim 80 mm high. Handle screw-on type, with 2 eyelets and 1 clamping band.

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	630
<b>Width of usable platform (mm)</b>	630
<b>Total height (mm)</b>	894
<b>Tyres</b>	Polyamide
<b>Wheel size (mm)</b>	80 x 35
<b>Version</b>	geschlossen
<b>Weight (kg)</b>	17
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976136103