


Transport equipment

Product data sheet

Article no.: 13650 Drum dolly

For upright transport or storage of 200 litre steel drums. Welded cross made of square pipe, with anti-slip corners, powder coated blue RAL 5007. 4 swivel castors, 2 with wheel lock, polyamide wheels, hubs with glide bearing.



Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	610
Width of usable platform (mm)	610
Total height (mm)	159
Tyres	Polyamide
Wheel size (mm)	80 x 35
Version	offen
Weight (kg)	6
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976913650