


Transport equipment

Product data sheet

Article no.: 1372 Euro box cart



Modular system: Tubular and sectional steel construction, bolted, powder coated blue RAL 5007. Variable use of shelf frames, distance 100 mm, angle when inclined 15° and 30°. 5 platforms with 10 Euro boxes 600 x 400 x 145 mm. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	820
Width of usable platform (mm)	610
Shelf heights (mm)	298, 598, 898, 1198, 1498
Load capacity per shelf (kg)	80
Total length (mm)	935
Total width (mm)	666
Total height (mm)	1686
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	67,5
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976513720