


**Transport equipment**

# Product data sheet

Article no.: 1399 Euro box cart



Modular system: Tubular and sectional steel construction, bolted, powder coated blue RAL 5007. Variable use of shelf frames, distance 150 mm, angle when inclined 15° and 30°. 5 platforms with 15 Euro boxes 600 x 400 x 145 mm. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	400
<b>Length of usable platform (mm)</b>	1240
<b>Width of usable platform (mm)</b>	610
<b>Shelf heights (mm)</b>	298, 598, 898, 1198, 1498
<b>Load capacity per shelf (kg)</b>	80
<b>Total length (mm)</b>	1372
<b>Total width (mm)</b>	685
<b>Total height (mm)</b>	1686
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	96
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976013992