


Transport equipment

Product data sheet

Article no.: 1580 Side frame cart



Tubular steel and profile steel welded, powder coated, surface durably protected, resistant to impact and scratches. Platform made of derived timber material boards, surface beech grain. With 4 high side frames. Height of side frames 750 mm. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	850
Width of usable platform (mm)	440
Height of loading platform (mm)	228
Total length (mm)	919
Total width (mm)	509
Total height (mm)	948
Tyres	TPE
Wheel size (mm)	160 x 40
Weight (kg)	29
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976015804