


Transport equipment

Product data sheet

Article no.: 1800 Table top cart



Modular system, platform and pushbar with screw connection, upper shelves can be inserted. Capacity upper and middle shelf 80 kg. Disassembled on delivery. Welded tubular or sectional steel construction, powder coated, blue RAL 5007. Shelves made of derived timber material board, beech decor surface. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



| | |
|---------------------------------------|---------------|
| Total load capacity (kg) | 200 |
| Length of usable platform (mm) | 850 |
| Width of usable platform (mm) | 500 |
| Shelf heights (mm) | 209, 515, 826 |
| Total length (mm) | 1030 |
| Total width (mm) | 500 |
| Total height (mm) | 1020 |
| Tyres | TPE |
| Wheel size (mm) | 125 x 32 |
| Weight (kg) | 34 |
| Country of origin | Germany |
| Warranty (years) | 10 |
| Customs tariff number | 87168000 |
| GTIN | 4017976018003 |