


**Transport equipment**

# Product data sheet

Article no.: 18312-1 Shelved trolley with tubes



Modular System: The Super-Multivario-Transporter is especially designed for heavy loads. High-quality elasticated solid-rubber wheels and hubs with ball bearings guarantee an extreme manoeuvrability and a smooth run. Steel tube and sectional steel welded, powder coated, blue RAL 5007. 1 fix and 3 variable shelves made of waterproof stable plywood boards. 1 side anti-slip the other side smooth. Variable use of shelves, minimum distance 100 mm. Capacity per shelf 180 kg. Ends of tubular construction with intermediate uprights at intervals of approx. 130 mm. Detachable side panels, also with intermediate uprights. 2 swivel and 2 fixed-wheel, elasticated solid rubber tyres blue-grey "trackless", hubs with ball bearings. Castors with wheel locks, according to the European Standard EN 1757-3

## Technical Details:



<b>Total load capacity (kg)</b>	1200
<b>Load capacity per shelf (kg)</b>	180
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	700
<b>Total length (mm)</b>	1184
<b>Total width (mm)</b>	724
<b>Total height (mm)</b>	1817
<b>Shelf heights (mm)</b>	283, 688, 1088, 1488
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 50
<b>Weight (kg)</b>	110
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976183121