


Transport equipment

Product data sheet

Article no.: 1892 ESD-mobile tilting stand



Electrostatic discharge construction. For plastic boxes, steel plate boxes, wire baskets etc., adjustable in height and mobile. Sectional steel-/ tubular construction with steel plate platform with single sided lay-on edge, inclinable by 15° und 30°, adjustable in height in intervals of 25 mm. Powder coating, slate grey RAL 7015. 4 swivel castors with TPE-ESD tyres, hubs with slide bearing. Brakes at 2 swivel castors according to the European Standard EN 1757-3 (safety of platform trolleys).

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	510
Width of usable platform (mm)	410
Angle of inclination (degree)	0, 15, 30
Height adjustable from-to (mm)	755-1105
Tyres	TPE-ESD
Wheel size (mm)	75 x 25
Weight (kg)	18,2
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976018928