


**Transport equipment**

# Product data sheet

Article no.: 2105 Storeroom trolley



Welded tubular and sectional steel, powder coated. 2 shelves made of derived timber material boards in angle steel frame, 12 mm high skirting. At the face ends wooden steps lifting automatically when released and standing firmly on the floor when under load, whereby the trolley is automatically locked. You can hold onto or lean against the safety handle provided. Steps can be tilted when in rest position. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	1000
<b>Width of usable platform (mm)</b>	600
<b>Shelf heights (mm)</b>	200, 820
<b>Load capacity per shelf (kg)</b>	80
<b>Total length (mm)</b>	1322
<b>Total width (mm)</b>	611
<b>Total height (mm)</b>	1155
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	45
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976021058