Product data sheet

Article no.: 2108 Storeroom trolley



Transport equipment



Welded tubular and sectional steel, powder coated. 4 shelves made of derived timber material boards in angle steel frame, 12 mm high skirting. At the face ends wooden steps lifting automatically when released and standing firmly on the floor when under load, whereby the trolley is automatically locked. You can hold onto or lean against the safety handle provided. Steps can be tilted when in rest position. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

Technical Details:







Total load capacity (kg)	250
Length of usable platform (mm)	1000
Width of usable platform (mm)	600
Shelf heights (mm)	200, 680, 1155, 1630
Load capacity per shelf (kg)	80
Total length (mm)	1322
Total width (mm)	611
Total height (mm)	1880
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	77
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976021089