


Transport equipment

Product data sheet

Article no.: 2166 Dolly

Frame made of angular steel, welded, powder coated, blue RAL 5007. With wooden platform covered with corrugated rubber. 4 swivel castors, wheels with TPE tyres, hubs with precision deep groove ball bearing. 2 swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).



Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	500
Width of usable platform (mm)	500
Height of loading platform (mm)	201
Total length (mm)	500
Total width (mm)	500
Total height (mm)	201
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	14
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976021669