


**Transport equipment**

# Product data sheet

Article no.: 2167 Dolly with gooseneck handle



Frame made of angular steel. Shaft with bolt connection, powder coated blue RAL 5007. Frame made of angular steel, with 1 plastic box 600 x 400 x 220 mm, without wooden platform. 2 swivel castors and 2 fixed-wheel castors. Wheels with TPE tyres, hubs with precision deep groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys).

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	610
<b>Width of usable platform (mm)</b>	410
<b>Height of loading platform (mm)</b>	209
<b>Total length (mm)</b>	890
<b>Total width (mm)</b>	410
<b>Total height (mm)</b>	860
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	13
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976021676