


**Transport equipment**

# Product data sheet

Article no.: 22811 Pallet dolly



For pallets and boxes. Sturdy sectional steel construction with 4 catch corners for stacking, powder coated. 2 castor wheels and 2 fixed wheels 200 x 50 mm. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Elasticated solid rubber tyres, blue-grey "trackless", hubs with ball bearings. Low rolling resistance, easy movement, no road noise. Optional extras are only delivered in a set with pallet dollies because they are welded together.

## Technical Details:



<b>Total load capacity (kg)</b>	1200
<b>Length of usable platform (mm)</b>	1210
<b>Width of usable platform (mm)</b>	810
<b>Height of loading platform (mm)</b>	282
<b>Total length (mm)</b>	1255
<b>Total width (mm)</b>	855
<b>Total height (mm)</b>	329
<b>Tyres</b>	Elastic solid rubber blue grey
<b>Wheel size (mm)</b>	200 x 50
<b>Version</b>	for euro pallets
<b>Weight (kg)</b>	35
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976228112