


Transport equipment

Product data sheet

Article no.: 22880 Pallet dolly



For pallets and boxes. Sturdy sectional steel construction with 4 catch corners for stacking, powder coated. 2 swivel and 2 fixed- wheels 200 x 50 mm. Swivel castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Polyamide wheels, hubs with roller bearings. Low rolling resistance, high chemical resistance, non marking. Road noise. Optional extras are only delivered in a set with pallet dollies because they are welded together.

Technical Details:



Total load capacity (kg)	1050
Length of usable platform (mm)	1010
Width of usable platform (mm)	810
Height of loading platform (mm)	282
Total length (mm)	1055
Total width (mm)	855
Total height (mm)	329
Tyres	Polyamide
Wheel size (mm)	200 x 50
Version	for industrial pallets
Weight (kg)	32
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976228808