


Transport equipment

Product data sheet

Article no.: 2358 Dolly

With platform made of beech plywood, with non-slip coating. 4 castors with solid rubber wheels 125 x 38 mm, blue-grey "trackless".



Technical Details:



Total load capacity (kg)	500
Length of usable platform (mm)	800
Width of usable platform (mm)	600
Height of loading platform (mm)	175
Total length (mm)	800
Total width (mm)	600
Total height (mm)	175
Tyres	Solid rubber blue-grey
Wheel size (mm)	125 x 38
Weight (kg)	10
Country of origin	Germany
Warranty (years)	10
Customs tariff number	44219999
GTIN	4017976023588