


Transport equipment

Product data sheet

Article no.: 23800 ESD-pallet dolly



Pallet dollies for pallets and lattice boxes. Sturdy sectional steel construction with 4 catch corners for stacking. Tubular steel and sectional steel welded, conductive powder coating, slate grey, RAL 7015. Screw and plug type construction. 2 swivel and 2 fixed-wheel castors with TPE-ESD tyres (thermoplastic elastomer), electrically conductive. Hubs with precision groove ball bearing. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are nonmarking.

Technical Details:



Total load capacity (kg)	750
Length of usable platform (mm)	1010
Width of usable platform (mm)	810
Height of loading platform (mm)	282
Total length (mm)	1055
Total width (mm)	855
Total height (mm)	329
Tyres	TPE-ESD
Wheel size (mm)	200 x 40
Version	for industrial pallets
Weight (kg)	33
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976238005