


**Transport equipment**

# Product data sheet

Article no.: 23891 Pallet dolly for tigger trains



Powder coated in blue RAL 5007. 3 swivel castors with polyamide wheels 200 x 50 mm white, hubs wit precision ball bearings but 1 castor is electrically conductive, black polypropylene wheel body, hub with precision ball bearings.. 2 swivel castors with full locking device in the lead, diagonal layout. Ground clearance: 235 mm

## Technical Details:



<b>Total load capacity (kg)</b>	1050
<b>Length of usable platform (mm)</b>	1210
<b>Width of usable platform (mm)</b>	810
<b>Height of loading platform (mm)</b>	280
<b>Total length (mm)</b>	1255
<b>Total width (mm)</b>	855
<b>Total height (mm)</b>	327
<b>Tyres</b>	Polyamide
<b>Wheel size (mm)</b>	200 x 50
<b>Version</b>	for tigger trains
<b>Weight (kg)</b>	34
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	73269098
<b>GTIN</b>	4017976238913