


Transport equipment

Product data sheet

Article no.: 23892 Pallet dolly for tigger trains



Powder coated in blue RAL 5007. 3 swivel castors with polyamide wheels 200 x 50 mm white, hubs wit precision ball bearings but 1 castor is electrically conductive, black polypropylene wheel body, hub with precision ball bearings.. 2 swivel castors with full locking device in the lead, diagonal layout. Ground clearance: 235 mm

Technical Details:



Total load capacity (kg)	1050
Length of usable platform (mm)	1210
Width of usable platform (mm)	1010
Height of loading platform (mm)	280
Total length (mm)	1255
Total width (mm)	1055
Total height (mm)	327
Tyres	Polyamide
Wheel size (mm)	200 x 50
Version	for tigger trains
Weight (kg)	34
Country of origin	Germany
Warranty (years)	10
Customs tariff number	73269098
GTIN	4017976238920