


**Transport equipment**

# Product data sheet

Article no.: 2390 Euro box cart



Tubular and sectional steel construction, bolted, powder coated. Open frame. Variable use of shelf frames, distance 50 mm, angle when inclined up to 15° and 30°. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	250
<b>Length of usable platform (mm)</b>	820
<b>Width of usable platform (mm)</b>	610
<b>Shelf heights (mm)</b>	238, 538, 838
<b>Load capacity per shelf (kg)</b>	80
<b>Total length (mm)</b>	935
<b>Total width (mm)</b>	666
<b>Total height (mm)</b>	1101
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	125 x 32
<b>Weight (kg)</b>	33
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976023908