


Transport equipment

Product data sheet

Article no.: 2391 Euro box cart



Tubular and sectional steel construction, bolted, powder coated. With 3 platforms with derived timber material boards, rim 10 mm high. Variable use of shelf frames, distance 50 mm, angle when inclined up to 15° and 30°. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 Swivel castors with wheel locks, according to European Standard EN1757-3 (safety of platform trolleys). Capacity upper and middle shelves 80 kg.

Technical Details:



Total load capacity (kg)	250
Length of usable platform (mm)	820
Width of usable platform (mm)	610
Shelf heights (mm)	251, 551, 851
Load capacity per shelf (kg)	80
Total length (mm)	935
Total width (mm)	666
Total height (mm)	1101
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	48
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976023915