


**Transport equipment**

# Product data sheet

Article no.: 24001430 Heavy table top cart with rigid PVC platforms



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves with weatherproof rigid PVC panel in dark grey. High chemical resistance, low flammability. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 200 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Length of usable platform (mm)</b>	850
<b>Width of usable platform (mm)</b>	500
<b>Shelf heights (mm)</b>	228, 860
<b>Total length (mm)</b>	1047
<b>Total width (mm)</b>	509
<b>Total height (mm)</b>	860
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	52
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976677927