


Transport equipment

Product data sheet

Article no.: 24021402 Table top cart with waterproof platforms



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 2 shelves with nonslip plywood board. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1000
Width of usable platform (mm)	700
Shelf heights (mm)	270, 900
Total length (mm)	1197
Total width (mm)	709
Total height (mm)	900
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	52
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976677866