


Transport equipment

Product data sheet

Article no.: 2403W Table top cart with steel plate trays



Modular system: Tubular steel and sectional steel, welded and powder coated, surface durably protected, resistant to impact and scratches. 2 platforms, trays made of steel sheet, with rim 10 mm high, welded oil-tight, powder coated. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	600
Length of usable platform (mm)	1200
Width of usable platform (mm)	800
Shelf heights (mm)	270, 900
Total length (mm)	1397
Total width (mm)	809
Total height (mm)	900
Tyres	TPE
Wheel size (mm)	200 x 40
Weight (kg)	66
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976224039