


**Transport equipment**

# Product data sheet

Article no.: 2432 Heavy workshop cart



Modular system: Steel tube and sectional steel welded, powder coated, surface durably protected, resistant to impact and scratches, platform made of derived timber material boards, surface beech grain. 1 lockable steel cupboard with leaf door, 1 fixed and 2 adjustable shelves. Powder coated, grey carcass RAL 7035, front blue RAL 5007. 2 swivel and 2 fixed-wheel castors, TPE tyres, hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Carrying capacity upper shelf 200 kg.

## Technical Details:



<b>Total load capacity (kg)</b>	600
<b>Length of usable platform (mm)</b>	1050
<b>Width of usable platform (mm)</b>	700
<b>Shelf heights (mm)</b>	270, 900
<b>Total length (mm)</b>	1197
<b>Total width (mm)</b>	709
<b>Total height (mm)</b>	900
<b>Tyres</b>	TPE
<b>Wheel size (mm)</b>	200 x 40
<b>Weight (kg)</b>	79
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976024325