


Transport equipment

Product data sheet

Article no.: 2445 Roller cupboard



Leaf-door cupboard, lockable, 1 fixed and 2 adjustable shelves, 500 mm wide, 600 mm deep and 600 mm high. Surface out of beech plywood, 22 mm thick with skirting on 3 sides, 80 mm high. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 swivel castors with wheel locks. Powder coated, carcass grey RAL 7035, front blue RAL 5007. Height of surface: 800 mm, total length: 650 mm, total width: 550 mm. Capacity per shelf 30 kg.

Technical Details:



Total load capacity (kg)	150
Length of usable platform (mm)	650
Width of usable platform (mm)	550
Total width (mm)	550
Total depth (mm)	650
Total height (mm)	875
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	35
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976024455