


Transport equipment

Product data sheet

Article no.: 2448 Rolling desk



Leaf-door cupboard, lockable, 1 fixed and 2 adjustable shelves, 500 mm wide, 600 mm deep and 600 mm high. Fit-on desk-top made of powder-coated steel plate. Desktop foldable. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 swivel castors with wheel locks. Powder coated, carcass grey RAL 7035, front blue RAL 5007. Height of surface: 1034, 1197 mm, total length: 650 mm, total width: 550 mm. Capacity per shelf 30 kg.

Technical Details:



Total load capacity (kg)	150
Surface height (mm)	1034, 1197
Total width (mm)	550
Total depth (mm)	650
Total height (mm)	1200
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	41
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976024486