


Transport equipment

Product data sheet

Article no.: 2449 Rolling desk



Cupboard of drawers, centrally lockable, 3 drawers 120 mm high and 1 drawer 180 mm high. Ball pull-out and pull-out lock. Fit-on desk-top made of powder-coated steel plate. Desktop foldable. 4 swivel castors with TPE tyres, hubs with groove ball bearing. 2 swivel castors with wheel locks. Powder coated, carcass grey RAL 7035, front blue RAL 5007. Height of surface: 1034/1197 mm, total length: 650 mm, total width: 550 mm. Capacity per drawer 25 kg.

Technical Details:



Total load capacity (kg)	150
Surface height (mm)	1034, 1197
Total width (mm)	550
Total depth (mm)	650
Total height (mm)	1200
Tyres	TPE
Wheel size (mm)	125 x 32
Weight (kg)	60
Country of origin	Germany
Warranty (years)	10
Customs tariff number	94032080
GTIN	4017976024493